



Strongly concentrated 3-in-1 wax dryer

Product Description

Blue Brilliant Polish is a strongly concentrated 3-in-1 drying, waxing and protection agent that meets the highest quality standard and can be used in every carwash installation.

Properties

Blue Brilliant Polish gives a showroom shine and a good paint protection.
Blue Brilliant Polish is suitable for PDI applications.
Blue Brilliant Polish can be applied as a hot or cold wax.
Blue Brilliant Polish does not contain silicones.

Direction of use

Carwashes:

- Dose between 0,1-0,2% of Blue Brilliant Polish in the water of the waxing arch.
- Use approximately 10 to 20 L water per car and 10 to 20ml product.
- Dry the car.
- For high pressure applications, weaker dosages can be sufficient.

Manual car washing:

- Dilute 10ml Blue Brilliant Polish at the last rinsing water, dry with a clean non-marking cloth.

Specifications

Physical state	Liquid
Colour	Blue
pH	ca. 5.5
Freezing point	-10 °C
Relative density	0.95
Solubility in water	100 %

Storage and Disposal

Keep only in the original container in a cool, well ventilated place. Keep container closed when not in use. Avoid release to the environment. Dispose in a safe manner in accordance with local/national regulations. Dispose of this material and its container at hazardous or special waste collection point.

Safety instructions for the user

Never let dry. Keep out of reach of children. Care should be taken to reduce the possibility of eye contact. In case of eye contact, rinse immediately with plenty of water. Obtain medical attention if pain, blinking, tears or redness persists. In case of inhalation, assure fresh air breathing. In case of skin contact, remove affected clothing and wash all exposed skin area with mild soap and water, followed by warm water rinse.

Please check the MSDS.

Not all CID LINES products are available in all countries. For information about availability of a specific product, please contact your CID LINES dealer.

KENOTEK

Waterpoortstraat 2, 8900 Ieper (Belgium)
T +32 (0)57 21 78 77 • F +32 (0)57 21 78 79 • www.kenotek.eu

